

WW 85 R  
Laundry tub, red  
with 22 (85) gll (l) l capacity.



- Suitable for FG 85
- Height (including handles) 34.5, width 80, depth 54 cm

EAN: 4002511097612 / Material number: 02084670 / Old Material Number: 59100005D

Product classification	
Washing machines	•
Tumble dryers	•
Rotary irons	•
Machine / accessory category	
HM 16-80	•
HM 16-83	•
PM 1210	•
PM 1214	•
PM 1217	•
PM 1318	•
PM 1418	•
PM 1421	•
PRI 318	•
PRI 418	•
D 500-1750	•
D 500-2000	•
D 500-2200	•
D 500-2500	•
D 500-3000	•
D 500-3300	•
D 600-1750	•
D 600-2000	•
D 600-2200	•
D 600-2500	•
D 600-3000	•
D 600-3300	•
D 800-1300	•
D 800-1750	•
D 800-2000	•
D 800-2200	•
D 800-2500	•
D 800-3000	•
D 800-3300	•
M 500-1750	•
M 500-2000	•
M 500-2200	•
M 500-2500	•
M 500-3000	•
M 500-3300	•
PM 1621	•
PM 1625	•
PM 1630	•
PM 1635	•
PM 1825	•
PM 1830	•
PM 1835	•
PT 5135 C	•
PT 5136	•
PT 5137 WP	•

WW 85 R  
Laundry tub, red  
with 22 (85) gll (l) l capacity.



EAN: 4002511097612 / Material number: 02084670 / Old Material Number: 59100005D

PT 5140 WP	•
PT 5141 WP	•
PT 5145 C	•
PT 5155 C	•
PT 5156	•
PT 5157 WP	•
PT 5186	•
PT 7186	•
PT 7188	•
PT 7135 C	•
PT 7136	•
PT 7137 WP	•
PT 7138	•
PT 8203	•
PT 8251	•
PT 8251 COP	•
PT 8253	•
PT 8257	•
PT 8257 WP	•
PT 8301	•
PT 8301 COP	•
PT 8303	•
PT 8331	•
PT 8331 COP	•
PT 8333	•
PT 8333 HW	•
PT 8337	•
PT 8337 HW	•
PT 8337 WP	•
PT 8401	•
PT 8403	•
PT 8403 HW	•
PT 8407	•
PT 8407 HW	•
PT 8503	•
PT 8503 HW	•
PT 8507	•
PT 8507 HW	•
PT 8803	•
PT 8803 HW	•
PT 8807	•
PT 8807 HW	•
PT 9136	•
PT 9137 WP	•
PW 413	•
PW 413 Mop Star 130	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5055	•
PW 5065	•

WW 85 R  
 Laundry tub, red  
 with 22 (85) gll (l) l capacity.

EAN: 4002511097612 / Material number: 02084670 / Old Material Number: 59100005D

PW 5064 MOP STAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOP STAR 80	•
PW 5104 MOP STAR 100	•
PW 5105 Vario	•
PW 5134 MOP STAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•
PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PW 9055	•
PW 9065	•
PWT 6089	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•
PW 200 Profi@Work	•
PT 200 Profi@Work	•
PDR 300 SmartBiz	•
PWM 300 SmartBiz	•
PDR 500-08	•
PDR 507	•
PDR 900-08	•
PDR 908	•
PIB 100	•
<b>Product category</b>	
Storage / transport system	•

WW 85 R  
Laundry tub, red  
with 22 (85) gll (l) l capacity.



EAN: 4002511097612 / Material number: 02084670 / Old Material Number: 59100005D

Product characteristics	
Electrical connection	OHNE
Material	Plastic
Colour	Red
Volume in l	22 (85) gll (l)
Dimensions and weight	
External dimensions, net height in mm	13 5/8 (345)
External dimensions, net width in mm	31 1/2 (800)
External dimensions, net depth in mm	21 3/8 (540)
External dimensions, gross height in mm	14 1/4 (360)
External dimensions, gross width in mm	31 1/2 (800)
External dimensions, gross depth in mm	21 3/8 (540)
Net weight [kg]	5 (2.00)
Gross weight in kg	5 (2.00)