

E 354

Clamps

Height-adjustable for optimum positioning of laboratory glassware on the nozzle.

EAN: 4002511117105 / Material number: 03809540 / Old Material Number: 69735401D



- Suitable for injector nozzle E 352
- Height adjustable locking
- Suitable for bottles, Erlenmeyer flasks and round bottomed flasks for example

<b>Product category</b>	
Glassware Washers, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
PG 8527	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
<b>Product category</b>	
Other accessories	•
<b>Product characteristics</b>	
Material	Wire, rilsan-coated, Stainless steel
Colour	Stainless Steel, White
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	5 15/16 (150) in (mm)
External dimensions, net width in mm	2 13/16 (70) in (mm)
External dimensions, net depth in mm	2 13/16 (70) in (mm)
External dimensions, gross height in mm	6 5/16 (160)
External dimensions, gross width in mm	3 15/16 (100)
External dimensions, gross depth in in (mm)	5 15/16 (150)
Net weight in kg	1 (0.05)
Gross weight in kg	1 (0.05)