

E 362

Blind stopper

For the sealing of fittings to load carriers.



- Thread M 8 x 1

EAN: 4002511117136 / Material number: 03809630 / Old Material Number: 69736201D

Product category	
Glassware Washers, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
Washer-disinfectors, medical	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8562	•
PG 8582	•
PG 8582 CD	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8592	•
PG 8593	•
Product category	
Other accessories	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Application area	
Reprocessing of laboratory glassware	•
Reprocessing of MIS instruments	•
Reprocessing of ophthalmology instruments	•
Reprocessing of robotic instruments	•
Reprocessing of surgical instruments	•
Reprocessing of lumened instruments	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	0 9/16 (14) in (mm)
External dimensions, net width in mm	0 7/16 (10) in (mm)
External dimensions, net depth in mm	0 7/16 (10) in (mm)
External dimensions, gross height in mm	4 3/4 (120)
External dimensions, gross width in mm	4 3/4 (120)
External dimensions, gross depth in in (mm)	6 3/4 (170)
Diameter in in (mm)	0 7/16 (10)
Net weight in kg	1 (0.00)
Gross weight in kg	1 (0.01)