

E 367

Mobile unit

for the optimum loading of intubation material.



- 20 nozzles Ø 2.5 x 30 mm, 25 nozzles Ø 4.0 x 30 mm (5 loose)
- 40 holding springs for nozzles
- Equipped with connection for hot air drying
- Bracket for ML/2 for wash cart recognition / spray arm control

EAN: 4002511116337 / Material number: 03809710 / Old Material Number: 69536701D

<b>Product category</b>	
Washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8535	•
PG 8536	•
<b>Product category</b>	
Mobile unit for anaesthesia instruments	•
<b>Product characteristics</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Application area</b>	
Reprocessing anaesthetic instruments	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	19 13/16 (502)
External dimensions, net width in in. (mm)	21 1/8 (535)
External dimensions, net depth in in. (mm)	20 5/16 (515)
External dimensions, gross height in in. (mm)	19 5/16 (490)
External dimensions, gross width in in. (mm)	21 5/16 (540)
External dimensions, gross depth in in (mm)	21 11/16 (550)
Net weight in lb (kg)	14 (6.20)
Gross weight in lb (kg)	23 (10.00)