

E 380  
Mobile unit  
for the optimum loading of narrow necked glassware.



- equipped with 32 nozzles and locking mechanisms
- Equipped with connection for hot air drying
- Bracket for ML/2 for automatic wash cart recognition

EAN: 4002511116467 / Material number: 03809880 / Old Material Number: 69538001D

<b>Product category</b>	
Glassware Washers, laboratory	•
<b>Machine affiliation</b>	
PG 8535	•
PG 8536	•
<b>Product category</b>	
Mobile unit with connection for hot-air drying	•
Mobile unit for narrow necked glassware	•
<b>Product characteristics</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Narrow necked glassware [number]	32
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	19 13/16 (502)
External dimensions, net width in in. (mm)	21 1/8 (535)
External dimensions, net depth in in. (mm)	20 3/8 (517)
External dimensions, gross height in in. (mm)	21 1/2 (545)
External dimensions, gross width in in. (mm)	6 5/16 (160)
External dimensions, gross depth in in (mm)	20 7/8 (530)
Net weight in lb (kg)	18 (7.90)
Gross weight in lb (kg)	19 (8.60)
<b>Accessory pack</b>	
E 351 injector nozzle, Ø 4 mm, length 160 mm [number]	14
E 352 injector nozzle, Ø 6 mm, length 220 mm [number]	18
E 353 clip for injector nozzle E 351 [number]	14
E 354 clip for injector nozzle E 352 [number]	18
Rinse nozzle for powder dispenser [number]	1