

E 314

Tap fitting

for the manual production of demineralized water.



- Pressurised to 10 bar
- Pressure-proof to 10 bar
- Including Pressure hose 150 cm
- Complete with pressure hose 150 cm

EAN: 4002511115286 / Material number: 03830340 / Old Material Number: 69431401D

Product category	
Fresh-water dishwashers	•
Throughfeed tank dishwashers	•
Glassware Washers, laboratory	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8063	•
PG 8164	•
PG 8165	•
PG 8166	•
PG 8169	•
PG 8172	•
PG 8172 Eco	•
PTD 901	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
PTD 701	•
PTD 702	•

E 314

Tap fitting

for the manual production of demineralized water.



EAN: 4002511115286 / Material number: 03830340 / Old Material Number: 69431401D

PTD 703	•
PTD 704	•
PG 8535	•
PG 8536	•
Product category	
Water treatment	•
Other accessories	•
Product characteristics	
Material	Plastic
Colour	Black
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	0 (0) in (mm)
External dimensions, net width in mm	0 (0) in (mm)
External dimensions, net depth in mm	0 (0) in (mm)
External dimensions, gross height in mm	5 3/8 (135)
External dimensions, gross width in mm	16 9/16 (420)
External dimensions, gross depth in in (mm)	8 5/16 (210)
Net weight in kg	4 (1.70)
Gross weight in kg	4 (1.81)