

E 315

Full demineralization single use resin

For the regeneration of full demineralization cartridges

EAN: 4002511115293 / Material number: 03830350 / Old Material Number: 69431501D



- 20 l of homogenously mixed resins
- For use in the LP 2800 empty cartridge
- Box with 2 bags at 10 litres
- Vacuum sealed in plastic bags
- Including filter bag for exchange

| Product category | |
|-------------------------------|---|
| Fresh-water dishwashers | • |
| Tank dishwashers | • |
| Throughfeed tank dishwashers | • |
| Glassware Washers, laboratory | • |
| Thermal disinfectors | • |
| Washer-disinfectors, medical | • |
| Machine affiliation | |
| G 8066 | • |
| PG 8067 | • |
| PG 8041 | • |
| PG 8043 | • |
| PG 8045 | • |
| PG 8055 | • |
| PG 8055 U | • |
| PG 8056 | • |
| PG 8056 U | • |
| PG 8057 TD | • |
| PG 8057 TD U | • |
| PG 8058 | • |
| PG 8058 U | • |
| PG 8059 | • |
| PG 8059 U | • |
| PG 8060 | • |
| PG 8061 | • |
| PG 8061 U | • |
| PG 8063 | • |
| PG 8164 | • |
| PG 8165 | • |
| PG 8166 | • |
| PG 8169 | • |
| PG 8172 | • |
| PG 8172 Eco | • |
| PTD 901 | • |
| PG 8096 | • |
| PG 8096 U | • |
| PG 8099 | • |
| PG 8099 U | • |
| PFD 400 | • |
| PFD 400 U | • |
| PFD 401 | • |
| PFD 401 U | • |
| PFD 402 | • |
| PFD 402 U | • |
| PFD 404 | • |
| PFD 404 U | • |
| PFD 405 | • |
| PFD 405 U | • |
| PFD 407 | • |
| PFD 407 U | • |

E 315

Full demineralization single use resin

For the regeneration of full demineralization cartridges

EAN: 4002511115293 / Material number: 03830350 / Old Material Number: 69431501D



| | |
|---|----------------|
| PFD 408 U | • |
| PTD 701 | • |
| PTD 702 | • |
| PTD 703 | • |
| PTD 704 | • |
| PG 8581 | • |
| PG 8582 | • |
| PG 8583 | • |
| PG 8583 CD | • |
| PG 8591 | • |
| PG 8592 | • |
| PG 8593 | • |
| Product category | |
| Water treatment | • |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0-0 |
| Frequency in Hz | 0-0 |
| Total rated load in kW | 0.00-0.00 |
| Fuse rating in A | 0-0 |
| Dimensions and weight | |
| External dimensions, gross height in in. (mm) | 5 1/8 (130) |
| External dimensions, gross width in in. (mm) | 15 3/4 (400) |
| External dimensions, gross depth in in. (mm) | 21 11/16 (550) |
| Net weight in lb (kg) | 30 (13.58) |
| Gross weight in lb (kg) | 32 (14.21) |