

E 402

Insert

for optimum loading of up to 44 watch glasses.



- Suitable for 44 watch glasses Ø 80 – 125 mm
- Equipped with 23 bars at a distance of 0 5/8 (15) in (mm)

EAN: 4002511116627 / Material number: 03830420 / Old Material Number: 69540201D

Product category	
Glassware Washers, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
G 7825	•
PG 8527	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
PLW 8615	•
PLW 8616	•
PLW 8617	•
PLW 6011	•
PLW 6111	•
PLW 8505	•
Product category	
Insert / module for watch glasses	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Distance between rails in mm	0 5/8 (15)
Application area	
Reprocessing of laboratory glassware	•
Capacity	
Watch glasses [number]	44
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	53
External dimensions, net width in mm	200
External dimensions, net depth in mm	445
External dimensions, gross height in mm	3 3/16 (80)
External dimensions, gross width in mm	8 11/16 (220)
External dimensions, gross depth in in (mm)	17 3/4 (450)
Net weight in kg	3 (0.92)
Gross weight in kg	3 (1.14)