

E 403

Insert

for optimum loading of up to 105 watch glasses.



- Suitable for 105 watch glasses Ø 50 – 60 mm
- Equipped with 36 bars at a distance of 0 3/8 (9) in (mm)

EAN: 4002511116634 / Material number: 03830430 / Old Material Number: 69540301D

Product category	
Glassware Washers, laboratory	•
Machine affiliation	
G 7823	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
PLW 8615	•
PLW 8616	•
PLW 8617	•
PLW 6011	•
PLW 6111	•
PLW 8505	•
Product category	
Insert / module for watch glasses	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Distance between rails in mm	0 3/8 (9)
Application area	
Reprocessing of laboratory glassware	•
Capacity	
Watch glasses [number]	105
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	1 7/16 (35) in (mm)
External dimensions, net width in mm	7 7/8 (200) in (mm)
External dimensions, net depth in mm	17 9/16 (445) in (mm)
External dimensions, gross height in mm	3 (75)
External dimensions, gross width in mm	20 1/8 (510)
External dimensions, gross depth in in (mm)	11 1/16 (280)
Net weight in kg	3 (1.32)
Gross weight in kg	4 (1.48)