


A 3

Cover net

As cover for wash items in inserts.



- Plastic coated metal frame with plastic netting
- Suitable for 1/4 inserts
- 206 x 206 mm

EAN: 4002511115606 / Material number: 03830470 / Old Material Number: 69500301D

<b>Product category</b>	
Glassware Washers, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
PG 8527	•
PG 8535	•
PG 8536	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8593	•
PLW 8615	•
PLW 8616	•
PLW 8617	•
PLW 6011	•
PLW 6111	•
PLW 8505	•
<b>Product category</b>	
Cover	•
<b>Product characteristics</b>	
Material	Wire, rilsan-coated, Plastic
Colour	Green, White, Black
<b>Application area</b>	
Reprocessing of laboratory glassware	•
Reprocessing of different utensils	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	0
External dimensions, net width in mm	206
External dimensions, net depth in mm	206
External dimensions, gross height in mm	0 7/16 (10)
External dimensions, gross width in mm	8 5/16 (210)
External dimensions, gross depth in in (mm)	7 7/8 (200)
Net weight in kg	1 (0.30)
Gross weight in kg	1 (0.32)