

E 454

Injector nozzle

for optimum cleaning of different wash items, such as trocar sleeves.



- Suitable for trocar sleeves with Ø 10-15 mm, 8 x 150 mm
- Equipped with a spring for height adjustment

EAN: 4002511908512 / Material number: 04203940 / Old Material Number: 69745401D

|   |                 |
|---|-----------------|
| <b>Product category</b>                     |                 |
| Washer-disinfectors, medical                | •               |
| Large-capacity washer-disinfectors, medical | •               |
| <b>Machine affiliation</b>                  |                 |
| G 7826                                      | •               |
| PG 8527                                     | •               |
| PG 8528                                     | •               |
| PG 8535                                     | •               |
| PG 8536                                     | •               |
| PG 8562                                     | •               |
| PG 8582                                     | •               |
| PG 8582 CD                                  | •               |
| PG 8592                                     | •               |
| <b>Product category</b>                     |                 |
| Injector nozzle                             | •               |
| <b>Product characteristics</b>              |                 |
| Material                                    | Stainless steel |
| Colour                                      | Stainless Steel |
| <b>Application area</b>                     |                 |
| Reprocessing of MIS instruments             | •               |
| Reprocessing of lumened instruments         | •               |
| <b>Standard electrical connection</b>       |                 |
| Number of phases                            | 0               |
| Voltage in V                                | 0               |
| Frequency in Hz                             | 0               |
| Total rated load in kW                      | 0.00            |
| Fuse rating in A                            | 0               |
| <b>Dimensions and weight</b>                |                 |
| External dimensions, net height in mm       | 0               |
| External dimensions, net width in mm        | 0               |
| External dimensions, net depth in mm        | 150             |
| External dimensions, gross height in mm     | 0 1/2 (12)      |
| External dimensions, gross width in mm      | 3 1/4 (80)      |
| External dimensions, gross depth in in (mm) | 4 3/4 (120)     |
| Diameter in in (mm)                         | 0 3/8 (8)       |
| Net weight in kg                            | 1 (0.03)        |
| Gross weight in kg                          | 1 (0.04)        |