


E 940

Mobile unit

for the optimum loading of narrow necked glassware on 2 levels.



- The mobile injector unit can also be used without the upper level
- Magnetic strip for automatic mobile unit recognition
- Lower level equipped with a total of 115 nozzles with clips

EAN: 4002512145473 / Material number: 04607630 / Old Material Number: 69594001D

| Product category | |
|---|--------------------------|
| Large-capacity washer-disinfectors, laboratory | • |
| Machine affiliation | |
| PG 8527 | • |
| Product category | |
| Mobile unit for narrow necked glassware | • |
| Product characteristics | |
| Material | Stainless steel, Plastic |
| Colour | Stainless Steel, Black |
| Application area | |
| Reprocessing of laboratory glassware | • |
| Capacity | |
| Narrow necked glassware [number] | 115 |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in in. (mm) | 22 1/4 (565) |
| External dimensions, net width in in. (mm) | 25 1/4 (640) |
| External dimensions, net depth in in. (mm) | 31 1/8 (790) |
| External dimensions, gross height in in. (mm) | 29 15/16 (760) |
| External dimensions, gross width in in. (mm) | 31 1/2 (800) |
| External dimensions, gross depth in in (mm) | 47 1/4 (1200) |
| Net weight in lb (kg) | 78 (35.00) |
| Gross weight in lb (kg) | 100 (45.00) |
| Accessory pack | |
| Magnetic strip for automatic program recognition (incl. magnets) [number] | 1 |