


E 444

Insert

for the optimum loading of cold-light cables and suction hoses.



- The cables/hoses are wound round the drum in a spiral form
- H 202 mm mm, with folding clamp 214 mm; Ø 5 3/4 (145) in (mm) mm

EAN: 4002512083966 / Material number: 04637700 / Old Material Number: 69544401D

Product classification	
Washer-disinfectors, medical	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8562	•
PG 8592	•
Product category	
Insert / module for MIS instruments	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Application area	
Reprocessing of MIS instruments	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	202
External dimensions, net width in mm	138
External dimensions, net depth in mm	112
External dimensions, gross height in mm	5 9/16 (140)
External dimensions, gross width in mm	5 15/16 (150)
External dimensions, gross depth in in (mm)	10 1/4 (260)
Diameter in in (mm)	5 3/4 (145)
Net weight in kg	1 (0.28)
Gross weight in kg	1 (0.44)