

E 460  
 Insert  
 for the optimum loading of different MIS instruments.



- Suitable for rigid fibre optics of different lengths
- Mesh width on the base 8 x 1 mm sides/lid 7 x 7 x 3 mm
- equipped with 3 brackets for 2 rigid fibre optics

EAN: 4002512183383 / Material number: 04861390 / Old Material Number: 69546001D

<b>Product category</b>	
Washer-disinfectors, medical	•
Large-capacity washer-disinfectors, medical	•
<b>Machine affiliation</b>	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8562	•
PG 8592	•
<b>Product category</b>	
Insert / module for MIS instruments	•
Other inserts	•
<b>Product characteristics</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Application area</b>	
Reprocessing of MIS instruments	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	53
External dimensions, net width in mm	100
External dimensions, net depth in mm	430
External dimensions, gross height in mm	3 3/4 (95)
External dimensions, gross width in mm	6 3/4 (170)
External dimensions, gross depth in in (mm)	21 3/4 (550)
Net weight in kg	2 (0.71)
Gross weight in kg	3 (0.94)