

E 884

Tray and platter insert, plastic coated

For the optimum loading of trays, racks and serving platters



- Suitable for lower basket U 890
- For 10 baking sheets, serving platters or trays
- Rail height 7 (175) in (mm), distance between rails 1 3/8 (32) in (mm)

EAN: 4002512259439 / Material number: 05018680 / Old Material Number: 67588401D

Product classification	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
Product category	
Insert for trays, baking sheets, serving platters	•
Product characteristics	
Material	Wire, rilsan-coated
Colour	White
Distance between rails in mm	1 3/8 (32)
Rail height in mm	7 (175)
For use in lower basket	U 890
Capacity	
Trays up to a size of 500 x 320 mm [number]	10
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0

E 884

Tray and platter insert, plastic coated

For the optimum loading of trays, racks and serving platters



EAN: 4002512259439 / Material number: 05018680 / Old Material Number: 67588401D

Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	175
External dimensions, net width in mm	460
External dimensions, net depth in mm	460
External dimensions, gross height in mm	19 (480)
External dimensions, gross width in mm	21 1/8 (535)
External dimensions, gross depth in in (mm)	7 3/4 (195)
Net weight in kg	4 (1.60)
Gross weight in kg	5 (2.20)