

E 485  
Bracket  
for the optimum loading of 3 kidney trays.



EAN: 4002512398725 / Material number: 05109210 / Old Material Number: 69548501D

|   |                 |
|---|-----------------|
| <b>Product category</b>                     |                 |
| Washer-disinfectors, medical                | •               |
| Large-capacity washer-disinfectors, medical | •               |
| <b>Machine affiliation</b>                  |                 |
| G 7823                                      | •               |
| G 7824                                      | •               |
| G 7825                                      | •               |
| G 7826                                      | •               |
| PG 8527                                     | •               |
| PG 8528                                     | •               |
| PG 8535                                     | •               |
| PG 8536                                     | •               |
| PG 8562                                     | •               |
| PG 8582                                     | •               |
| PG 8582 CD                                  | •               |
| PG 8592                                     | •               |
| PG 8593                                     | •               |
| <b>Product category</b>                     |                 |
| Insert for kidney dishes / basins           | •               |
| <b>Product characteristics</b>              |                 |
| Material                                    | Stainless steel |
| Colour                                      | Stainless Steel |
| <b>Application area</b>                     |                 |
| Reprocessing of kidney dishes               | •               |
| <b>Capacity</b>                             |                 |
| Kidney dishes [number]                      | 3               |
| <b>Standard electrical connection</b>       |                 |
| Number of phases                            | 0               |
| Voltage in V                                | 0               |
| Frequency in Hz                             | 0               |
| Total rated load in kW                      | 0.00            |
| Fuse rating in A                            | 0               |
| <b>Dimensions and weight</b>                |                 |
| External dimensions, net height in mm       | 195             |
| External dimensions, net width in mm        | 80              |
| External dimensions, net depth in mm        | 464             |
| External dimensions, gross height in mm     | 2 13/16 (70)    |
| External dimensions, gross width in mm      | 11 1/16 (280)   |
| External dimensions, gross depth in in (mm) | 19 15/16 (505)  |
| Net weight in kg                            | 1 (0.41)        |
| Gross weight in kg                          | 2 (0.56)        |