


E 743

Module

for the optimum loading of narrow necked glassware 100 - 500 ml.



- With 36 nozzles (E 351) 4 x 160 mm with clips (E 353)

EAN: 4002512591164 / Material number: 05555250 / Old Material Number: 69574301D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
G 7825	•
G 7826	•
<b>Product category</b>	
Insert / module for narrow necked glassware	•
<b>Product characteristics</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Narrow necked glassware [number]	36
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	7 1/2 (190)
External dimensions, net width in in. (mm)	19 3/8 (492)
External dimensions, net depth in in. (mm)	19 9/16 (496)
External dimensions, gross height in in. (mm)	6 3/4 (170)
External dimensions, gross width in in. (mm)	20 7/8 (530)
External dimensions, gross depth in in (mm)	22 1/16 (560)
Net weight in lb (kg)	22 (9.70)
Gross weight in lb (kg)	23 (10.00)