


E 750

Frames

for the optimum securing of different inserts.



- Holding frames for securing inserts E 106 to E 111
- Enables loading with E 135 for baby bottles in E 555/2
- Enables loading with E 135 for baby bottles in E 735/2

EAN: 4002512606288 / Material number: 05567510 / Old Material Number: 69575001D

Product category	
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
Product category	
Other inserts	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Application area	
Reprocessing of baby bottles	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	1 1/2 (37)
External dimensions, net width in in. (mm)	21 7/16 (544)
External dimensions, net depth in in. (mm)	19 3/16 (486)
External dimensions, gross height in in. (mm)	22 1/2 (570)
External dimensions, gross width in in. (mm)	23 5/8 (600)
External dimensions, gross depth in in (mm)	21 11/16 (550)
Net weight in lb (kg)	2 (0.85)
Gross weight in lb (kg)	3 (1.00)