

E 908/1

Insert

For separable MIS instruments/work inserts or fibre optics.



- Mesh width 8 x 1 mm (base), sides enclosed
- Interior sections individually adjustable with 4 bars
- Hook for hanging in E 906/1

EAN: 4002513252286 / Material number: 05704010 / Old Material Number: 69590802D

Product category	
Washer-disinfectors, medical	•
Machine affiliation	
PG 8536	•
Product category	
Insert / module for MIS instruments	•
Product characteristics	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Application area	
Reprocessing of MIS instruments	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	5 1/8 (130) in (mm)
External dimensions, net width in mm	18 1/8 (460) in (mm)
External dimensions, net depth in mm	1 7/16 (36) in (mm)
External dimensions, gross height in mm	5 15/16 (150)
External dimensions, gross width in mm	19 15/16 (505)
External dimensions, gross depth in in (mm)	3 15/16 (100)
Net weight in kg	2 (0.68)
Gross weight in kg	2 (0.85)