

DOS-G2

Pump casing in stainless steel

With space for a maximum of 3 pumps P2 for dispensing liquid media.



- 12-pole terminal strip for easy connection

EAN: 4002513310610 / Material number: 05760630 / Old Material Number: 59170112USA

Product category	
Washing machines	•
Machine / accessory category	
PW 413	•
PW 418	•
PW 5134 MOP STAR 130	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
Product category	
Dispenser system	•
Product characteristics	
Electrical connection	OHNE
Dimensions and weight	
External dimensions, net height in in. (mm)	21 5/16 (540)
External dimensions, net width in in. (mm)	21 5/16 (540)
External dimensions, net depth in in. (mm)	7 1/2 (190)
External dimensions, gross height in in. (mm)	7 5/16 (185)
External dimensions, gross width in in. (mm)	21 5/16 (540)
External dimensions, gross depth in in. (mm)	21 5/16 (540)
Net weight in lbs (kg)	6 (2.30)
Gross weight in lbs (kg)	6 (2.50)