

UC 30-90/60-78

Box base

to raise the machine incl. side unit, 60 cm deep, 90 cm wide.



- Suitable for all machines, width 90, depth 60 cm
- Can be screwed onto the appliance

EAN: 4002513347791 / Material number: 05818080 / Old Material Number: 69379008D

Product category	
Glassware Washers, laboratory	•
Product category	
Plinth / base	•
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, gross height in in. (mm)	14 5/8 (370)
External dimensions, gross width in in. (mm)	39 1/2 (1002)
External dimensions, gross depth in in. (mm)	27 3/16 (690)
Net weight in lb (kg)	26 (11.60)
Gross weight in lb (kg)	29 (13.10)