

E 741/1

Mobile unit

for the optimum loading of modules on 1 - 4 levels.



- Depending on size of the wash items up to 3 modules can be used
- Coupling of the mobile unit to the water and drying air supply
- The vertical clearance for the individual levels is different

EAN: 4002513512267 / Material number: 06070360 / Old Material Number: 69574102D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
G 7825	•
G 7826	•
Product category	
Other mobile units	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Application area	
Reprocessing of laboratory glassware	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	26 13/16 (680)
External dimensions, net width in in. (mm)	20 7/8 (530)
External dimensions, net depth in in. (mm)	23 5/8 (600)
External dimensions, gross height in in. (mm)	21 11/16 (550)
External dimensions, gross width in in. (mm)	25 1/4 (640)
External dimensions, gross depth in in (mm)	25 5/8 (650)
Net weight in lb (kg)	27 (12.00)
Gross weight in lb (kg)	29 (12.80)