

MF/3

Trolleys

for loading & unloading washer-&disinfectors.



- For easy handling of the mobile instrument unit
- With lifting technology operated by foot pressure
- Equipped with 2 lockable castors
- Infeed height 751 mm, +/- 100 mm

EAN: 4002513771114 / Material number: 06392900 / Old Material Number: 69200107D

Product category	
Glassware Washers, laboratory	•
Washer-disinfectors, medical	•
Machine affiliation	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
Product category	
Storage / transport system	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in in. (mm)	46 9/16 (1182)
External dimensions, net width in in. (mm)	26 (660)
External dimensions, net depth in in. (mm)	31 13/16 (807)
External dimensions, gross height in in. (mm)	16 15/16 (430)
External dimensions, gross width in in. (mm)	31 1/2 (800)
External dimensions, gross depth in in. (mm)	47 1/4 (1200)
Net weight in lb (kg)	76 (34.20)
Gross weight in lb (kg)	116 (52.40)