

E 474/4

Basic mobile unit

for optimum loading of up to 2 MIS sets in a modular system.



- For hollow instruments in 3 insert modules
- Equipped with connection for hot air drying
- For: E 903, E 905, E 906, E 444, E 460, E 457, E 142
- Bracket for ML/2 for wash cart recognition / spray arm control

EAN: 4002513805536 / Material number: 06439160 / Old Material Number: 69547405D

Product category	
Washer-disinfectors, medical	•
Machine affiliation	
PG 8536	•
Product category	
Mobile unit for MIS instruments	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Application area	
Reprocessing of MIS instruments	•
Reprocessing of dental instruments	•
Capacity	
MIS sets [number]	2
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	20 (507)
External dimensions, net width in in. (mm)	21 1/8 (535)
External dimensions, net depth in in. (mm)	20 5/16 (515)
External dimensions, gross height in in. (mm)	21 5/16 (540)
External dimensions, gross width in in. (mm)	21 5/16 (540)
External dimensions, gross depth in in (mm)	24 13/16 (630)
Net weight in lb (kg)	23 (10.17)
Gross weight in lb (kg)	23 (10.17)
Accessory pack	
E 362 blind stopper [number]	2
E 447 female adapter, for male Luer Lock [number]	3