

E 729

Insert

for optimum loading of up to 4-5 ophthalmic theatre sets on 3 levels.



- 2 levels for 4 DIN mesh trays
- 1 level with 16 or 30 injector nozzles
- Connection option for E 478/1 to the inlet pipe
- Equipped with connection for hot air drying
- Magnetic strip for mobile unit recognition (without magnets ML)

EAN: 4002513893274 / Material number: 06517580 / Old Material Number: 69572901D

Product category	
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
G 7825	•
G 7826	•
Product category	
Mobile unit for ophthalmology instruments	•
Product characteristics	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Application area	
Reprocessing of ophthalmology instruments	•
Capacity	
DIN mesh trays [number]	4
SPRI mesh trays [number]	2
Surgery sets for micro instruments [number]	4-5
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	18 9/16 (471)
External dimensions, net width in in. (mm)	20 7/8 (530)
External dimensions, net depth in in. (mm)	23 5/8 (600)
External dimensions, gross height in in. (mm)	26 13/16 (680)
External dimensions, gross width in in. (mm)	22 1/16 (560)
External dimensions, gross depth in in (mm)	25 5/8 (650)
Net weight in lb (kg)	32 (14.40)
Gross weight in lb (kg)	37 (16.40)
Accessory pack	
E 476 holder [number]	1
E 477 stopper [number]	1
E 790 Luer Lock connection element female to female [number]	8
E 791 Luer Lock connection element female to male [number]	8
Magnetic strip for automatic program recognition (without magnets) [number]	1