


E 950/1

Mobile unit

for the optimum loading of narrow necked glassware on 3 levels.



- Equipped with 232 nozzles
- Levels 1+3: Each 80 nozzles ID 90 (2.5 x 90 mm)
- Level 2: 72 nozzles ID 90 (2.5 x 90 mm)
- Maximum vertical clearance on all three levels 148 mm each

EAN: 4002514072708 / Material number: 06696990 / Old Material Number: 69595002D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PG 8527	•
<b>Product category</b>	
Mobile unit for narrow necked glassware	•
<b>Product characteristics</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Narrow necked glassware [number]	232
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	22 9/16 (572)
External dimensions, net width in in. (mm)	25 1/4 (640)
External dimensions, net depth in in. (mm)	31 1/8 (790)
External dimensions, gross height in in. (mm)	25 5/8 (650)
External dimensions, gross width in in. (mm)	25 5/8 (650)
External dimensions, gross depth in in. (mm)	32 5/16 (820)
Net weight in lb (kg)	63 (28.20)
Gross weight in lb (kg)	89 (40.00)
<b>Accessory pack</b>	
Magnetic strip for automatic program recognition (incl. magnets) [number]	1