

E 901/2

Mobile unit

for the optimum loading of mesh trays/basins and hollow instruments.



- Equipped with 3 integrated spray arms
- The loading areas for the individual levels are different
- The loading capacity for the individual levels are different
- Equipped with connection for hot air drying
- Magnetic strip for wash cart recognition (incl. magnets ML)

EAN: 4002514219882 / Material number: 06893870 / Old Material Number: 69590103D

<b>Product category</b>	
Large-capacity washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8527	•
PG 8528	•
<b>Product category</b>	
Mobile unit for inserts	•
Mobile unit for MIS instruments	•
Mobile unit for basins	•
Mobile unit for mesh trays	•
<b>Product characteristics</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Application area</b>	
Reprocessing of MIS instruments	•
Reprocessing of surgical instruments	•
Reprocessing of lumened instruments	•
<b>Capacity</b>	
DIN mesh trays [number]	12
SPRI mesh trays [number]	4
Lumened instruments [number]	8
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	23 1/4 (590)
External dimensions, net width in in. (mm)	25 1/4 (640)
External dimensions, net depth in in. (mm)	31 1/8 (790)
External dimensions, gross height in in. (mm)	28 3/8 (720)
External dimensions, gross width in in. (mm)	32 11/16 (830)
External dimensions, gross depth in in (mm)	30 3/4 (780)
Net weight in lb (kg)	59 (26.50)
Gross weight in lb (kg)	67 (30.00)
<b>Accessory pack</b>	
E 362 blind stopper [number]	3
E 447 female adapter, for male Luer Lock [number]	2
E 449 male adapter, for female Luer Lock [number]	2
E 980 angled adapter [number]	3
Injector nozzle, Ø 4 mm, length 110 mm [number]	4
Injector nozzle, Ø 4 mm, length 120 mm, with spring clip [number]	3
Magnetic strip for automatic program recognition (incl. magnets) [number]	1