


U 535 Basket

with low top frame for the optimum loading of 25 glasses up to 20 cm tall.




- With 25 compartments
- Compartment size 3 9/16 (90) in (mm) x 3 9/16 (90) in (mm) mm
- Includes extender set comprising short and long extenders
- Height adjustable top frame extendable up to 20 cm
- Width 50, depth 50 cm, width with Gastronorm (GN) sides 53 cm

EAN: 4002514278735 / Material number: 06984150 / Old Material Number: 67653501D

| Product category | |
|------------------------------|---|
| Fresh-water dishwashers | • |
| Tank dishwashers | • |
| Throughfeed tank dishwashers | • |
| Machine affiliation | |
| G 8066 | • |
| PG 8067 | • |
| PG 8041 | • |
| PG 8043 | • |
| PG 8045 | • |
| PG 8055 | • |
| PG 8055 U | • |
| PG 8056 | • |
| PG 8056 U | • |
| PG 8057 TD | • |
| PG 8057 TD U | • |
| PG 8058 | • |
| PG 8058 U | • |
| PG 8059 | • |
| PG 8059 U | • |
| PG 8060 | • |
| PG 8061 | • |
| PG 8061 U | • |
| PG 8165 | • |
| PG 8166 | • |
| PG 8169 | • |
| PG 8172 | • |
| PG 8172 Eco | • |
| PTD 901 | • |
| PG 8096 | • |
| PG 8096 U | • |
| PG 8099 | • |
| PG 8099 U | • |
| PFD 400 | • |
| PFD 400 U | • |
| PFD 401 | • |
| PFD 401 U | • |
| PFD 402 | • |
| PFD 402 U | • |
| PFD 404 | • |
| PFD 404 U | • |
| PFD 405 | • |
| PFD 405 U | • |
| PFD 407 | • |
| PFD 407 U | • |
| PFD 408 U | • |
| PTD 702 | • |
| PTD 703 | • |
| PTD 704 | • |

U 535
Basket

with low top frame for the optimum loading of 25 glasses up to 20 cm tall.



EAN: 4002514278735 / Material number: 06984150 / Old Material Number: 67653501D

| Product category | |
|---|----------------|
| Basket for glasses | • |
| Product characteristics | |
| Material | Plastic |
| Colour | Blue |
| Number of compartments | 25 |
| Compartment width in mm | 3 9/16 (90) |
| Compartment length in mm | 3 9/16 (90) |
| Capacity | |
| Glasses 110–140 mm high [number] | 25 |
| Glasses 175–200 mm high [number] | 25 |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in in. (mm) | 7 7/8 (200) |
| External dimensions, net width in in. (mm) | 19 11/16 (500) |
| External dimensions, net depth in in. (mm) | 19 11/16 (500) |
| External dimensions, gross height in in. (mm) | 8 11/16 (220) |
| External dimensions, gross width in in. (mm) | 21 11/16 (550) |
| External dimensions, gross depth in in. (mm) | 21 11/16 (550) |
| Net weight in lb (kg) | 6 (2.50) |
| Gross weight in lb (kg) | 7 (3.00) |