

O 188/2  
Upper basket  
for the optimum loading of different inserts.



- Vertical clearance: 165 mm, height adjustable +/- 20 mm
- With integrated magnetic spray arm
- Magnet for use with spray arm sensors for PG 8535, PG 8536

EAN: 4002514556178 / Material number: 07333030 / Old Material Number: 69118802D

<b>Product category</b>	
Glassware Washers, laboratory	•
Washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8535	•
PG 8536	•
<b>Product category</b>	
Carrier / basket carrier	•
Upper basket	•
<b>Product characteristics</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	11 1/16 (280)
External dimensions, net width in in. (mm)	8 1/2 (215)
External dimensions, net depth in in. (mm)	18 3/4 (475)
External dimensions, gross height in in. (mm)	11 1/4 (285)
External dimensions, gross width in in. (mm)	21 5/16 (540)
External dimensions, gross depth in in (mm)	21 7/8 (555)
Net weight in lb (kg)	6 (2.40)
Gross weight in lb (kg)	7 (3.16)