

O 190/2

Upper basket

for the optimum loading of different inserts.



- Vertical clearance: 8 1/2 (215) in (mm) mm
- With integrated magnetic spray arm
- Magnet for use with spray arm sensors for PG 8535, PG 8536

EAN: 4002514556185 / Material number: 07333050 / Old Material Number: 69119002D

Product category	
Glassware Washers, laboratory	•
Washer-disinfectors, medical	•
Machine affiliation	
PG 8535	•
PG 8536	•
Product category	
Carrier / basket carrier	•
Upper basket	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Maximum vertical clearance in mm	8 1/2 (215)
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	10 7/16 (265)
External dimensions, net width in in. (mm)	20 15/16 (531)
External dimensions, net depth in in. (mm)	18 3/4 (475)
External dimensions, gross height in in. (mm)	11 1/4 (285)
External dimensions, gross width in in. (mm)	21 5/16 (540)
External dimensions, gross depth in in (mm)	21 7/8 (555)
Net weight in lb (kg)	6 (2.40)
Gross weight in lb (kg)	8 (3.19)