

E 327/1

Mobile unit

for the optimum loading of 4 DIN mesh trays.



- Suitable for 4 DIN mesh trays on 2 levels
- Magnet for use with spray arm sensors for PG 8535, PG 8536
- With integrated magnetic spray arm
- Bracket for ML/2 for wash cart recognition / spray arm control

EAN: 4002514556239 / Material number: 07333100 / Old Material Number: 69532702D

| | |
|---|-----------------|
| Product category | |
| Washer-disinfectors, medical | • |
| Machine affiliation | |
| PG 8535 | • |
| PG 8536 | • |
| Product category | |
| Mobile unit for mesh trays | • |
| Product characteristics | |
| Material | Stainless steel |
| Colour | Stainless Steel |
| Application area | |
| Reprocessing of surgical instruments | • |
| Capacity | |
| DIN mesh trays [number] | 4 |
| SPRI mesh trays [number] | 2 |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in in. (mm) | 16 3/16 (410) |
| External dimensions, net width in in. (mm) | 20 7/8 (530) |
| External dimensions, net depth in in. (mm) | 22 1/2 (570) |
| External dimensions, gross height in in. (mm) | 16 9/16 (420) |
| External dimensions, gross width in in. (mm) | 21 5/16 (540) |
| External dimensions, gross depth in in (mm) | 23 7/16 (595) |
| Net weight in lb (kg) | 6 (2.40) |
| Gross weight in lb (kg) | 8 (3.30) |