

MF 27/28-1

Transfer cart

for loading & unloading washer-&disinfectors.



- Equipped with 4 castors, 2 of which can be locked
- Simple and convenient handling thanks to rounded handles
- Dockable or lockable to rolling conveyor etc. with both sides
- Infeed height 850 mm, -100 mm, +150 mm
- With removable drip tray H 70, W 603, D 866 mm

EAN: 4002514594026 / Material number: 07397640 / Old Material Number: 69200111D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
PG 8527	•
PG 8528	•
Product category	
Storage / transport system	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in in. (mm)	41 3/8 (1050)
External dimensions, net width in in. (mm)	29 3/16 (740)
External dimensions, net depth in in. (mm)	36 5/8 (930)
External dimensions, gross height in in. (mm)	39 13/16 (1010)
External dimensions, gross width in in. (mm)	28 3/4 (730)
External dimensions, gross depth in in. (mm)	37 7/16 (950)
Net weight in lb (kg)	71 (32.00)
Gross weight in lb (kg)	100 (45.00)