

E 943/2

Module

for the optimum loading of narrow necked glassware 100 - 500 ml.



- 32 nozzles (E 351) 4 x 160 mm with clips (E 353)

EAN: 4002514605043 / Material number: 07459400 / Old Material Number: 69594303D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PG 8527	•
PG 8528	•
Product category	
Insert / module for narrow necked glassware	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Application area	
Reprocessing of laboratory glassware	•
Capacity	
Narrow necked glassware [number]	32
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	7 1/2 (190)
External dimensions, net width in in. (mm)	22 (558)
External dimensions, net depth in in. (mm)	13 7/8 (352)
External dimensions, gross height in in. (mm)	7 1/8 (180)
External dimensions, gross width in in. (mm)	22 1/16 (560)
External dimensions, gross depth in in (mm)	21 11/16 (550)
Net weight in lb (kg)	15 (6.50)
Gross weight in lb (kg)	17 (7.50)