

E 936

Insert

for optimum loading of up to 15 lamp handles.



EAN: 4002514811260 / Material number: 07759480 / Old Material Number: 69593601D

<b>Product category</b>	
Large-capacity washer-disinfectors, medical	•
<b>Machine affiliation</b>	
G 7823	•
G 7824	•
G 7826	•
PG 8527	•
PG 8528	•
<b>Product category</b>	
Other inserts	•
<b>Product characteristics</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Application area</b>	
Reprocessing of surgical instruments	•
<b>Capacity</b>	
Lamp handles [number]	15
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	3 9/16 (90)
External dimensions, net width in in. (mm)	9 11/16 (245)
External dimensions, net depth in in. (mm)	19 11/16 (500)
External dimensions, gross height in in. (mm)	5 1/8 (130)
External dimensions, gross width in in. (mm)	10 7/8 (275)
External dimensions, gross depth in in (mm)	20 7/8 (530)
Net weight in lb (kg)	2 (0.50)
Gross weight in lb (kg)	3 (0.92)