

E 735/2

Mobile unit

for the optimum loading of instruments on 3 levels.



- Equipped with 2 integrated spray arms
- The loading areas for the individual levels are different
- Magnetic strip for mobile unit recognition (without magnets ML)

EAN: 4002514816388 / Material number: 07765710 / Old Material Number: 69573503D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
G 7825	•
G 7826	•
Product category	
Mobile unit for inserts	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Capacity	
DIN mesh trays [number]	6
SPRI mesh trays [number]	3
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	21 3/4 (552)
External dimensions, net width in in. (mm)	20 7/8 (530)
External dimensions, net depth in in. (mm)	23 5/8 (600)
External dimensions, gross height in in. (mm)	25 5/8 (650)
External dimensions, gross width in in. (mm)	21 11/16 (550)
External dimensions, gross depth in in (mm)	25 1/4 (640)
Net weight in lb (kg)	24 (10.80)
Gross weight in lb (kg)	29 (12.80)
Accessory pack	
Magnetic strip for automatic program recognition (without magnets) [number]	1