

## PT 7186 Vario [EL]

Vented dryer, electric heating

with a shortest cycle time of 37 min for a high laundry throughput.



- Drum volume 6.36 (180.00) ft<sup>3</sup> (l), load size 18 (8.0) lb (kg)
- Large program variety – application-specific drying programs
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002515128718 / Material number: 09294650 / Old Material Number: 52718663USA

Construction type and design	
Construction type	Front loader
Product line	Octoplus
Front	Octo blue
Load in lbs. (kg)	18 (8.0)
Load ratio	1:2,5
Drum volume in l	6.36 (180.00) ft <sup>3</sup> (l)
Drying system	Vented system
Door opening [Ø] in in. (mm)	17 3/8 (440)
Door-opening angle in degrees	180
Door hinging	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for small businesses	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for medical and dental practices	•
Performance data	
Maximum evaporation capacity in l/hour	8.10
Program duration in minutes	37
Controls	
Control type	Profitronic L Vario
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Program sequence indicator	•
Control panel with plain text	•
Choice of display language	•
Standard / target grp programs	
Basic programs	•
Programs for facility management	•
Programs for dry cleaners	•
Programs for fire departments and rescue services	•
Programs for stud farms / riding schools / stables	•
Programs for private households	•
Standard electrical connection	
Heating type	Electric
Electrical connection	2 AC 208V 60HZ
Electric heater rating in kW	4.34

## PT 7186 Vario [EL]

Vented dryer, electric heating

with a shortest cycle time of 37 min for a high laundry throughput.



EAN: 4002515128718 / Material number: 09294650 / Old Material Number: 52718663USA

Total rated load in kW	4.84
Fuse rating in A	30
NEMA plug: Twist Lock L6-30	•
<b>Dimensions and weight of dryer</b>	
External dimensions, net height in in. (mm)	40 3/16 (1020)
External dimensions, net width in in. (mm)	27 9/16 (700)
External dimensions, net depth in in. (mm)	30 1/16 (763)
External dimensions, gross height in in. (mm)	47 7/8 (1215)
External dimensions, gross width in in. (mm)	29 15/16 (760)
External dimensions, gross depth in in. (mm)	32 5/16 (820)
Net weight in lbs. (kg)	170 (77.0)
Gross weight in lbs. (kg)	195 (88)
Maximum floor load in N/m <sup>2</sup>	1000
<b>Emission values</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.62
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Dryer basket (optional)	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system	•
RS 232 serial interface (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
<b>Capacities</b>	
Breathing masks [number]	4
Protective suits [number]	1-2
Protective coats [number]	1-2
Synthetic duvets [number]	1
Synthetic pillows [number]	1-2
Down comforters [number]	1
Down pillows [number]	1-2
Cleaning cloths, 22 g [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Horse summer blankets [number]	1-2
<b>Standards / certs / symbols</b>	
Splash protection IPX4	•
Complies with Machinery Directive 2006/42/EC	•