


O 892

Upper basket

With insert E 812 and 2 support rails for a variety of glassware



- Height adjustable in 2 positions by 5 cm
- The brackets ensure a secure hold for long stemmed glasses
- With integrated spray arm, connection at the back
- Max. vertical clearance 7 7/8 (200) in (mm)
- The glassware insert E 812 is included

EAN: 4002515276372 / Material number: 09548990 / Old Material Number: 67189201D

Product category	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
Product category	
Basket for glasses	•
Upper basket	•
Product characteristics	
Material	Wire, rilsan-coated
Colour	White
Maximum vertical clearance in mm	7 7/8 (200)
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0

O 892

Upper basket

With insert E 812 and 2 support rails for a variety of glassware

EAN: 4002515276372 / Material number: 09548990 / Old Material Number: 67189201D



Dimensions and weight	
External dimensions, net height in in. (mm)	7 1/2 (190)
External dimensions, net width in in. (mm)	20 7/16 (518)
External dimensions, net depth in in. (mm)	19 3/16 (486)
External dimensions, gross height in in. (mm)	20 7/8 (530)
External dimensions, gross width in in. (mm)	11 1/4 (285)
External dimensions, gross depth in in. (mm)	20 7/8 (530)
Net weight in lb (kg)	7 (2.97)
Gross weight in lb (kg)	7 (3.12)