

PT 8807 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



- Drum volume 28.25 (800.00) ft³ (l), load size 32.0-40.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Simple operation – easy to clean large fluff filter

EAN: 4002515480977 / Material number: 09906740 / Old Material Number: 52880705USA

Construction type and design	
Construction type	Front loader
Product line	Professional
Front	Stainless steel
Load in lbs. (kg)	32.0-40.0
Load ratio	1:25-1:20
Drum volume in l	28.25 (800.00) ft ³ (l)
Drying system	Vented system
Door opening [Ø] in in. (mm)	20 1/2 (520)
Door-opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Performance data	
Maximum evaporation capacity in l/hour	37 (37) gal (US)/min (l)
Program duration in minutes	29
Tested operating hours	20000
Controls	
Control type	Profitronic M
Programmability	Freely programmable
Program controls	Residual moisture controlled
Max. delay start in h	Can be selected freely
Time left display	•
Program sequence indicator	•
Choice of display language	•
Standard / target grp programs	
Basic programs	•
Programs for hotels and restaurants	•
Programs for retirement and care homes	•
Programs for facility management	•
Programs for dry cleaners	•
Programs for fire departments and rescue services	•
Programs for stud farms / riding schools / stables	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3 AC 208V 60HZ
Electric heater rating in kW	25.70

PT 8807 [PTM EL BSS ARP]

Vented dryer, electric heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002515480977 / Material number: 09906740 / Old Material Number: 52880705USA

Total rated load in kW	27.40
Fuse rating in A	90
Dimensions and weight	
External dimensions, net height in in. (mm)	64 5/8 (1640)
External dimensions, net width in in. (mm)	47 1/2 (1206)
External dimensions, net depth in in. (mm)	54 1/2 (1384)
External dimensions, gross height in in. (mm)	69 9/16 (1766)
External dimensions, gross width in in. (mm)	54 3/4 (1390)
External dimensions, gross depth in in. (mm)	58 1/16 (1474)
Net weight in lbs. (kg)	633 (287.0)
Gross weight in lbs. (kg)	739 (335)
Maximum floor load in N/m ²	3708
Emission values	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.98
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface lint filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecyclingPlus	•
Low temperature function	•
Communication slot	•
Emergency shut-off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
RS 232 serial interface (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management	•
Operating data logging	•
Capacities	
Breathing masks [number]	16
Protective suits [number]	6
Protective coats [number]	9
Synthetic duvets [number]	4
Synthetic pillows [number]	8
Down comforters [number]	4
Down pillows [number]	8
Cleaning cloths, 22 g [number]	727
Cotton mops, 40 cm [number]	168
Cotton mops, 50 cm [number]	145
Microfibre mops, 40 cm [number]	267
Microfibre mops, 50 cm [number]	188
Horse summer blankets [number]	4-5
Standards / certs / symbols	
CE	•
Splash protection IPX4	•
Complies with Machinery Directive 2006/42/EC	•