

PT 8407 [PTM D ARP]

Vented dryer, steam heating

With individually programmable controls for the maximum in flexibility.



- Drum volume 14.13 (400.00) ft³ (l) l (l), load capacity 16.0-20.0 kg (KG)
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Simple operation – easy to clean large fluff filter

EAN: 4002515491638 / Material number: 09925010 / Old Material Number: 52840745USA

Construction type and version	
Construction type	Front loader
Product line	Professional
Front	Stainless steel
Load in lbs. (kg)	16.0-20.0
Load ratio	1:25-1:20
Drum volume in l	14.13 (400.00) ft ³ (l)
Drying system	Vented
Door opening [Ø] in in. (mm)	20 1/2 (520)
Door-opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Performance data	
Maximum evaporation capacity in l/hour	21.90
Program duration in minutes	28
Tested operating hours	20000
Controls	
Control type	Profitronic M
Programmability	Freely programmable
Program controls	Residual moisture controlled
Max. delay start in h	Freely selectable
Time left display	•
Program sequence indicator	•
Choice of display language	•
Standard and target group programs	
Basic programs	•
Programs for hotels and restaurants	•
Programs for retirement and care homes	•
Programs for facility management	•
Programs for dry cleaners	•
Programs for fire departments and rescue services	•
Programs for stud farms / riding schools / stables	•
Standard electrical connection	
Heating type	Steam
Electrical connection	3 AC 208V 60HZ
Electric heater rating in kW	0.00

PT 8407 [PTM D ARP]

Vented dryer, steam heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002515491638 / Material number: 09925010 / Old Material Number: 52840745USA

Steam heater rating in kW	28.00
Total rated load in kW	1.30
Fuse rating in A	10
Possible voltage variant 1	
Electrical connection	3 AC 220-240V 60HZ
Heater rating in kW	0.00
Total rated load in kW	1.30
Fuse rating in A	10
Dimensions and weight	
External dimensions, net height in in. (mm)	55 1/8 (1400)
External dimensions, net width in in. (mm)	35 3/4 (906)
External dimensions, net depth in in. (mm)	45 7/8 (1164)
External dimensions, gross height in in. (mm)	60 1/8 (1526)
External dimensions, gross width in in. (mm)	43 (1090)
External dimensions, gross depth in in. (mm)	49 3/8 (1254)
Net weight in lbs. (kg)	478 (216.5)
Gross weight in lbs. (kg)	530 (240)
Maximum floor load in N	2408
Emission levels	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2.64
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface lint filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecyclingPlus	•
Low temperature function	•
Communication slot	•
Emergency shut-off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
RS 232 serial interface (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Operating data logging	•
Capacity	
Breathing masks [number]	16
Protective suits [number]	3
Protective coats [number]	4
Synthetic duvets [number]	2
Synthetic pillows [number]	4
Down comforters [number]	2
Down pillows [number]	4
Cleaning cloths, 22 g [number]	370
Cotton mops, 40 cm [number]	84
Cotton mops, 50 cm [number]	73
Microfibre mops, 40 cm [number]	133
Microfibre mops, 50 cm [number]	94

PT 8407 [PTM D ARP]

Vented dryer, steam heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002515491638 / Material number: 09925010 / Old Material Number: 52840745USA

Horse summer blankets [number]

2-3

Test certificates and symbols

CE

•

Splash protection IPX4

•

Complies with Machinery Directive 2006/42/EC

•