

FM

FlowMeter

For measuring the through flow volume and display for changing the cartridge.

EAN: 4002515537107 / Material number: 10008910 / Old Material Number: 67809701D



- Suitable for partial demineralization cartridges
- Optical and acoustic display for cartridge change
- One-line display, connection to external LED possible
- Includes wall bracket
- Includes power unit

Product classification	
Fresh-water dishwashers	•
Tank dishwashers	•
Throughfeed tank dishwashers	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8164	•
PG 8165	•
PG 8166	•
PG 8169	•
PG 8172	•
PG 8172 Eco	•
PTD 901	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PTD 701	•
PTD 702	•
PTD 703	•
PTD 704	•

FM

FlowMeter

For measuring the through flow volume and display for changing the cartridge.

EAN: 4002515537107 / Material number: 10008910 / Old Material Number: 67809701D



Product category	
Water treatment	•
Product characteristics	
Material	Plastic
Colour	Black
Dimensions and weight	
External dimensions, net height in mm	110
External dimensions, net width in mm	125
External dimensions, net depth in mm	52
External dimensions, gross height in mm	6 1/8 (155)
External dimensions, gross width in mm	12 1/4 (310)
External dimensions, gross depth in in (mm)	13 7/8 (350)
Net weight in kg	5 (1.85)
Gross weight in kg	6 (2.49)