

DE-CS6-85

Appliance lid

Cover for top of machine incl. side unit, 60 cm deep, 90 cm wide.

EAN: 4002515604380 / Material number: 10101450 / Old Material Number: 69216010D



- Usable for Aqua Purificator PG 8595 and DOS cabinet PG 8596
- combined with 60 cm washer-disinfector (e.g., PG 8581 or PG 8591)

Product classification	
Glassware Washers, laboratory	•
Thermal disinfectors	•
Washer-disinfectors, medical	•
Machine affiliation	
PG 8581	•
PG 8562	•
PG 8582	•
PG 8504	•
PG 8583	•
PG 8591	•
PG 8592	•
PG 8593	•
Product category	
Lid	•
Product characteristics	
Material	Stainless steel
Colour	Stainless Steel
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	15
External dimensions, net width in mm	900
External dimensions, net depth in mm	600
External dimensions, gross height in mm	3 1/4 (80)
External dimensions, gross width in mm	39 (990)
External dimensions, gross depth in in (mm)	31 1/8 (790)
Net weight in kg	15 (6.70)
Gross weight in kg	20 (9.00)