

UBS 2

Conversion kit

for use with selected series G 78 mobile units in PG 85 machines.



- For older injector trolleys without drying unit connection

EAN: 4002515588987 / Material number: 10131100 / Old Material Number: 69215015D

Product category	
Glassware Washers, laboratory	•
Machine affiliation	
PG 8583	•
PG 8593	•
Product category	
Conversion kit	•
Product characteristics	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	3 9/16 (90) in (mm)
External dimensions, net width in mm	5 1/8 (129) in (mm)
External dimensions, net depth in mm	11 5/8 (295) in (mm)
External dimensions, gross height in mm	4 15/16 (125)
External dimensions, gross width in mm	6 1/2 (165)
External dimensions, gross depth in in (mm)	13 13/16 (350)
Net weight in kg	2 (0.51)
Gross weight in kg	2 (0.71)