

PG 8061 U [MK HYGIENE]

Built-under fresh-water dishwasher

With baskets, for high hygiene requirements at care homes, childcare, etc. (NSF/ANSI 3). ADA compliant.



- Max. cleaning performance*: 152 plates/h
- First-class results thanks to freshwater wash system
- Particularly hygienic results – final rinse temperature 85°C
- Safe and easy operation – automatic door opening
- Versatile processing of two wire or plastic baskets per cycle

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002515592250 / Material number: 10147190 /

Old Material Number: 61806125CDN

Construction type and design

Construction type	Built-under dishwasher
Product line	Professional
Model	Hygiene
Wash system	Fresh water dishwasher
Number of wash levels	2
Front	Stainless steel
Side panels	Stainless steel
Can be converted to a freestanding appliance	Stand 1-80, stainless steel

Application

Suitable for retirement and care homes	•
Suitable for small restaurants/bars	•
Suitable for the hospitality industry	•
Suitable for guesthouses	•
Suitable for cafeterias	•
Suitable for kindergartens	•
Suitable for fast food restaurants	•

Performance data

Circulation pump, Qmax in gal/min (l/min.)	103 (390)
Shortest program duration in minutes	15
Maximum final rinse temperature in °F (°C)	185 (85)
Cleaning performance, plates/h	152
Cleaning performance, baskets/h	8
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	15000

Controls

Control type	TouchControl
Program selection	Touch on metal
Max. delay start in h	24
Time left display	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Adjustable wash temperature	•
Adjustable wash time	•
Program sequence indicator	•
Choice of display language	•
Language-neutral operation	•

Standard electrical connection

Electrical connection	2 PH. 240V 60HZ
Heater rating in kW	5.40
Total rated load in kW	5.80
Fuse rating in A	30
Length of power cord in ft. (m)	7 (2.20)

Possible voltage variant 1

Electrical connection	3 PH. 240V 60HZ
Heater rating in kW	5.40
Total rated load in kW	5.80
Fuse rating in A	20

PG 8061 U [MK HYGIENE]

Built-under fresh-water dishwasher

With baskets, for high hygiene requirements at care homes, childcare, etc. (NSF/ANSI 3). ADA compliant.



EAN: 4002515592250 / Material number: 10147190 /

Old Material Number: 61806125CDN

Water connection/drainage

Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain pump [DN]	22
Maximum drain pump height (delivery head) in in. (cm)	39 3/8 (100)
Integrated water softener	•
Maximum water hardness in gpg (mmol/l)	62.59 (10.70)
Water protection system	Waterproof system
Water consumption per wash cycle in gal (l)	2.1 (8.00) gll (l)

Dimensions and weight

External dimensions, height in in. (mm)	32 5/16 (820)
External dimensions, width in in. (mm)	23 9/16 (598)
External dimensions, depth in in. (mm)	23 7/16 (595)
External dimensions, gross height in in. (mm)	37 1/16 (940)
External dimensions, gross width in in. (mm)	26 5/8 (675)
External dimensions, gross depth in in. (mm)	27 (685)
Usable space in wash cabinet, height in in. (mm)	22 1/16 (559)
Usable space in wash cabinet, width in in. (mm)	20 7/8 (530)
Usable space in wash cabinet, depth of upper basket in in. (mm)	18 11/16 (474)
Usable space in wash cabinet, depth of lower basket in in. (mm)	19 15/16 (505)
Rack height above floor in in. (mm)	8 9/16 (216)
Net weight lb [kg]	139 (63)
Gross weight in lb (kg)	153 (69)
Maximum floor load in N/m ²	1200

Emission values

Emission sound pressure level at workplace (LpA)	45 dB(A) re 20 µPa
Sound power level LwA	57.0
Heat dissipation into the room in MJ/h	1.08

Programs

Normal Plus / Universal	•
Normal / QuickIntenseWash	•
Intensive / Pots & Pans	•
Reactivation	•
Drain	•

Basket design

1 x upper basket O 891 for cups	•
1 x lower basket U 890 for inserts	•
1 x insert E 810 for dessert plates	•
2 x insert E 816 for plates	•
2 x insert E 165 for cutlery	•
Height-adjustable upper basket	•

Features

Drying	AutoOpen assisted drying
AutoClose	•
1 combi dispensing unit in the door for powder cleaning agent and rinsing agent	•

PG 8061 U [MK HYGIENE]

Built-under fresh-water dishwasher

With baskets, for high hygiene requirements at care homes, childcare, etc. (NSF/ANSI 3). ADA compliant.



EAN: 4002515592250 / Material number: 10147190 /

Old Material Number: 61806125CDN

In-door salt container	•
Perfect GlassCare	•
Aerosol steam condenser	•
Wash cabinet made of high-quality stainless steel	•
Optical interface	•
A wide range of accessories (optional)	•
Connection options	
External dispenser module for liquid cleaning agent	•
External dispenser module for rinsing agent	•
Standards / certs / symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
EMC	•
Interference suppression	•
VDE	•
EN 1717	•