

HM16-80 D [EL]

Rotary iron, electric

with steam function for optimum results and maximum convenience.



- Performance 13.0 kg/h*, roller diameter 6 5/16 (160) in (mm), working width 32 11/16 (830) in (mm)
- Iron comfortably while seated
- Work at your own pace thanks to variable roller speed
- Durable roller padding – aramid needle felt cloth
- Easy to store – fold-away function

* With 20% residual moisture – performance data according to DIN 11 902: The achievable laundry throughput depends on overall conditions such as, for example, the type of laundry and the experience of the operator.

EAN: 4002515636459 / Material number: 10238590 / Old Material Number: 53168002USA

Construction type and design	
Construction type	In-feed and out-feed of laundry at the front
Installation against a wall possible	•
Product line	Professional
Outer casing	Lotus white
Roller diameter in in. (mm)	6 5/16 (160)
Working width in in. (mm)	32 11/16 (830)
Heater plate material	Aluminium
Iron padding	Polyester needle-felt cloth
Roller cover	ARAMID needle-felt cloth
Application	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for residential homes and apartments	•
Suitable for commercial laundromats	•
Suitable for offshore use	•
Suitable for Marine use	•
Suitable for camp sites	•
Suitable for domestic use	•
Performance data	
Max. ironing performance at 20% residual moisture in kg/h	13.0
Tested operating hours	2500
Controls	
Control type	Selector dial
Touch display (optional)	Drehwahlschalter
Minimum iron speed, controlled in m/min	2.0
Maximum iron speed, controlled in m/min	4.5
Adjustable temperature	In temperature stages
Standard electrical connection	
Heating type	Electric
Electrical connection	2AC 208-240V 50-60HZ
Electric heater rating in kW	2.80-3.70
Boiler heater rating in kW	0.85
Total rated load in kW	2.90-3.80
Fuse rating in A	20
NEMA plug: 6-20	•
Dimensions and weight	
External dimensions, height in in. (mm)	37 13/16 (959)
External dimensions, width in in. (mm)	38 13/16 (985)
External dimensions, depth in in. (mm)	15 (380)
External dimensions, gross height in in. (mm)	22 1/2 (570)
External dimensions, gross width in in. (mm)	44 1/8 (1120)
External dimensions, gross depth in in. (mm)	17 3/4 (450)
Net weight in lbs. (kg)	86 (39)
Gross weight in lbs. (kg)	100 (45)
Maximum floor load in N/m ²	382
Features	
Steam function	•
Free roller end	•

HM16-80 D [EL]

Rotary iron, electric

with steam function for optimum results and maximum convenience.



EAN: 4002515636459 / Material number: 10238590 / Old Material Number: 53168002USA

Fold-away function	•
Automatic finger guard / finger guard	•
Foot switch	•
Airing bar	•
Feed board	•
Laundry return feed	•
Machine-independent accessories	•
Standards / certs / symbols	
CSA-C-US	•
Complies with Machinery Directive 2006/42/EC	•