

HM16-80 D [EL]

Rotary iron, electric

with steam function for optimum results and maximum convenience.



- Performance 28.6 (13.0) lb/h (kg/h) kg/h*, roller diameter 6 5/16 (160) in (mm), working width 32 11/16 (830) in (mm)
- Iron comfortably while seated
- Work at your own pace thanks to variable roller speed
- Durable roller padding – aramid needle felt cloth
- Easy to store – fold-away function

* With 20% residual moisture – performance data according to DIN 11 902: The achievable laundry throughput depends on overall conditions such as, for example, the type of laundry and the experience of the operator.

EAN: 4002515636459 / Material number: 10238590 /
Old Material Number: 53168002USA

Construction type and design

| | |
|--------------------------------------|--|
| Construction type | In-feed and out-feed of laundry at the front |
| Installation against a wall possible | • |
| Product line | Professional |
| Outer casing | Lotus white |
| Roller diameter in in. (mm) | 6 5/16 (160) |
| Working width in in. (mm) | 32 11/16 (830) |
| Heater plate material | Aluminium |
| Iron padding | Polyester needle-felt cloth |
| Roller cover | ARAMID needle-felt cloth |

Application

| | |
|---|---|
| Suitable for hotels and restaurants | • |
| Suitable for retirement and care homes | • |
| Suitable for residential homes and apartments | • |
| Suitable for commercial laundromats | • |
| Suitable for offshore use | • |
| Suitable for Marine use | • |
| Suitable for camp sites | • |
| Suitable for domestic use | • |

Performance data

| | |
|---|-------------|
| Max. ironing performance at 20% residual moisture in kg/h | 28.6 (13.0) |
| Tested operating hours | 2500 |

Controls

| | |
|---|-----------------------|
| Control type | Selector dial |
| Touch display (optional) | Drehwahlschalter |
| Minimum iron speed, controlled in m/min | 2.0 |
| Maximum iron speed, controlled in m/min | 4.5 |
| Adjustable temperature | In temperature stages |

Standard electrical connection

| | |
|------------------------------|----------------------|
| Heating type | Electric |
| Electrical connection | 2AC 208-240V 50-60HZ |
| Electric heater rating in kW | 2.80-3.70 |
| Boiler heater rating in kW | 0.85 |
| Total rated load in kW | 2.90-3.80 |
| Fuse rating in A | 20 |
| NEMA plug: 6-20 | • |

Dimensions and weight

| | |
|---|----------------|
| External dimensions, height in in. (mm) | 37 13/16 (959) |
| External dimensions, width in in. (mm) | 38 13/16 (985) |
| External dimensions, depth in in. (mm) | 15 (380) |
| External dimensions, gross height in in. (mm) | 22 1/2 (570) |
| External dimensions, gross width in in. (mm) | 44 1/8 (1120) |
| External dimensions, gross depth in in. (mm) | 17 3/4 (450) |
| Net weight in lbs. (kg) | 86 (39) |
| Gross weight in lbs. (kg) | 100 (45) |
| Maximum floor load in N | 382 |

HM16-80 D [EL]

Rotary iron, electric

with steam function for optimum results and maximum convenience.



EAN: 4002515636459 / Material number: 10238590 /
Old Material Number: 53168002USA

Features

| | |
|---------------------------------------|---|
| Steam function | • |
| Free roller end | • |
| Fold-away function | • |
| Automatic finger guard / finger guard | • |
| Foot switch | • |
| Airing bar | • |
| Feed board | • |
| Laundry return feed | • |
| Machine-independent accessories | • |

Standards / certs / symbols

| | |
|--|---|
| CSA-C-US | • |
| Complies with Machinery Directive 2006/42/EC | • |