

A 208

Mobile unit

For the optimum loading of 8 mesh trays.



- High capacity: simultaneous reprocessing of 8 DIN mesh trays
- 4 additional connections for hollow instruments
- Removable level increases vertical clearance if required

EAN: 4002515809242 / Material number: 10616030 / Old Material Number: 69620800D

Product category	
Washer-disinfectors, medical	•
Machine affiliation	
PG 8582	•
PG 8582 CD	•
PG 8592	•
Product category	
Mobile unit for mesh trays	•
Product characteristics	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Application area	
Reprocessing of mesh trays	•
Capacity	
DIN mesh trays [number]	8
Lumened instruments [number]	4
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in in. (mm)	15 11/16 (397)
External dimensions, net width in in. (mm)	20 7/8 (529)
External dimensions, net depth in in. (mm)	21 1/2 (546)
External dimensions, gross height in in. (mm)	10 11/16 (270)
External dimensions, gross width in in. (mm)	20 11/16 (525)
External dimensions, gross depth in in (mm)	21 5/16 (540)
Net weight in lb (kg)	10 (4.40)
Gross weight in lb (kg)	15 (6.40)