

DP [50Hz]

Drain pump

For converting appliances with drain valves to drain pumps.



- For installations without a floor drain

EAN: 4002516024057 / Material number: 10931330 / Old Material Number: 69240003D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PLW 8615	•
PLW 8616	•
PLW 8617	•
<b>Product characteristics</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black, White, Grey
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	0 (0) in (mm)
External dimensions, net width in mm	0 (0) in (mm)
External dimensions, net depth in mm	0 (0) in (mm)
External dimensions, gross height in mm	7 1/8 (180)
External dimensions, gross width in mm	15 3/8 (390)
External dimensions, gross depth in in (mm)	15 3/8 (390)
Net weight in kg	9 (3.88)
Gross weight in kg	13 (5.73)