

APLW 001

Mobile unit

For optimum loading of laboratory glassware on the lowest level.



- Maximum loading width: 470 mm
- Maximum loading depth: 490 mm

EAN: 4002516115298 / Material number: 11104480 / Old Material Number: 69300100D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PLW 6011	•
PLW 6111	•
<b>Product category</b>	
Insert / module for beakers	•
Mobile unit for inserts	•
<b>Product characteristics</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel
<b>Application area</b>	
Reprocessing of laboratory glassware	•
<b>Dimensions and weight</b>	
External dimensions, net height in mm	135
External dimensions, net width in mm	535
External dimensions, net depth in mm	582
External dimensions, gross height in mm	7 1/2 (190)
External dimensions, gross width in mm	22 1/8 (560)
External dimensions, gross depth in in (mm)	24 1/8 (610)
Net weight in kg	10 (4.20)
Gross weight in kg	14 (5.90)