

PWM 908 [EL DP-1]

Professional washing machine (208/240V) with electric heating, drain pump, short program cycle times and specialized programs.



- Drum volume 2.58 (73) ft³ (l), load size 20 (9.0) lb (kg)
- 22% less water consumption and 28% less energy consumption*
- Tested for intensive use – unique Miele quality
- Maximum user comfort with touch colour display – M Touch Flex
- Thorough cleaning thanks to professional wash programs

* Based on the Cottons 60°C program with a hot water connection, compared to the predecessor model.

EAN: 4002516229414 / Material number: 11204460 /
Old Material Number: 51908159NAM

Construction type and design

Construction type	Front-loader, stackable
Product line	Performance Plus
Front	Lotus white
Control panel colour	Stainless steel
Load in lbs. (kg)	20 (9.0)
Drum volume in l	2.58 (73) ft ³ (l)
Door opening [Ø] in in. (mm)	11 13/16 (300)
Door-opening angle in degrees	167
Door hinging	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated rear wall made of stainless steel	•

Application

Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for laundromats	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for small businesses	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for medical and dental practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday resorts	•
Suitable for public / community facilities	•

Performance data

Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6.10
Specific energy consumption for cold water connection in kWh/kg	0.12
Specific water consumption for hot water connection in l/kg	5.80
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	55.0
Energy consumption with cold water connection in kWh	1.10
Program duration with cold water connection in minutes	59
Water consumption with hot water connection in l	52.0
Energy consumption with hot water connection in kWh	0.57
Program duration with hot water connection in minutes	49
Residual moisture with cold rinse in %	48

PWM 908 [EL DP-1]

Professional washing machine (208/240V) with electric heating, drain pump, short program cycle times and specialized programs.



EAN: 4002516229414 / Material number: 11204460 /
Old Material Number: 51908159NAM

Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g-factor	704
Tested operating hours	30000
Controls	
Control type	M Touch Flex
Programmability	programmable
Max. delay start in h	96
Time left display	•
Program sequence indicator	•
Language can be selected easily at any time	•
Dispensing	
Detergent drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensing	•
Standard electrical connection	
Heating type	Electric
Electrical connection	2~ 208-240V 60HZ
Heater rating in kW	3.80-5.00
Total rated load in kW	4.00-5.20
Fuse rating in A	30
NEMA plug: Twist Lock L6-30	•
Water connection/drainage	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
Dimensions and weight	
External dimensions, net height in in. (mm)	33 1/2 (850)
External dimensions, net width in in. (mm)	23 1/2 (596)
External dimensions, net depth in in. (mm)	28 1/8 (714)
External dimensions, gross height in in. (mm)	37 1/16 (940)
External dimensions, gross width in in. (mm)	26 (660)
External dimensions, gross depth in in. (mm)	30 1/4 (768)
Net weight in lbs. (kg)	230 (104.0)
Gross weight in lbs. (kg)	239 (108)
Maximum floor load in N	2820
Emission values	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00
Features	
3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•

PWM 908 [EL DP-1]

Professional washing machine (208/240V) with electric heating, drain pump, short program cycle times and specialized programs.



EAN: 4002516229414 / Material number: 11204460 /
Old Material Number: 51908159NAM

Disinfection rinse	•
EcoSpeed	•
SoftSteam	•
Efficient scoop rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load recognition	•
Volumetric flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Adding laundry	•
Machine-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	95
Connection options	
Payment system (optional)	•
Optical interface for service access	•
LAN / WiFi module (optional)	•
WiFiConn@ct	•
Standards / certs / symbols	
CE	•
Splash protection IPX4	•
WEEE	•