

DU 900 RV

Drying unit, with ventilation slots, electric

For 900 mm-wide appliances and optimal internal and external drying of items.

EAN: 4002516265177 / Material number: 11382320 / Old Material Number: 69250006USA



- With top-box panelling; air supply via the room.
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash cabinet
- Air flow rate 250 m³/h
- HEPA filter service life: 1,000 hours

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
Dimensions and weight	
External dimensions, net height in mm	840
External dimensions, net width in mm	845
External dimensions, net depth in mm	1045
External dimensions, gross height in mm	39 (990)
External dimensions, gross width in mm	33 3/8 (845)
External dimensions, gross depth in in (mm)	47 1/4 (1200)
Net weight in kg	256 (116.00)
Gross weight in kg	294 (133.00)